

suction gripper ESG-10X30

Part number: 189188

FESTO



Exemplary representation

Data sheet

Overall data sheet – Individual values depend upon your configuration.

| Feature | Value |
|---|---|
| suction cup size | 10x30 mm |
| Assembly position | Vertical |
| Design structure | Vacuum connection at top Vacuum connection at side with height compensation With long height compensator |
| Correlation to suction-cup holder | Size 4 |
| Suction cup shape | Oval, flat |
| Operating medium | Atmospheric air based on ISO 8573-1:2010 [7:--] |
| Corrosion resistance classification CRC | 1 - Low corrosion stress |
| Ambient temperature | -10 ... 70 °C |
| Vacuum connection | M14x1 G1/8 QS-6 PK-4 |
| Materials note | Conforms to RoHS |
| Material suction cup | NBR |