

suction cup holder

ESH-HCL-4-QS

Part number: 189229

FESTO

with increased height compensator, vacuum connection at top,
compensator secured by two hexagonal nuts.



Data sheet

| Feature | Value |
|---|---|
| Height compensator for suction-cup holder | 20 mm |
| Volume | 1.78 cm ³ |
| Assembly position | Vertical |
| Design structure | Vacuum connection at top with height compensation |
| Correlation to suction-cup holder | Size 4 |
| Operating medium | Atmospheric air based on ISO 8573-1:2010 [7:-:-] |
| Corrosion resistance classification CRC | 1 - Low corrosion stress |
| PWIS conformity | VDMA24364-A1-L |
| Ambient temperature | 0 ... 60 °C |
| Product weight | 47 g |
| Mounting type | with lock nut |
| suction cup mounting | M6 |
| Vacuum connection | QS-6 |
| Materials note | Conforms to RoHS |
| Material seals | NBR Steel |
| Material bracket | Aluminium Nickel-plated brass POM Heat-treatment steel High alloy steel |