

# suction cup ESS-30X90-ON

Part number: 189418

FESTO

easily interchangeable,



## Data sheet

Feature	Value
Nominal size	6 mm
suction cup size	30x90 mm
suction cup volume	10.17 cm <sup>3</sup>
Position of connection	on top
Assembly position	Any
Correlation to suction-cup holder	Size 5
Suction cup shape	Oval, flat
Operating pressure MPa	-95 ... 0 kPa
Operating pressure	-0.95 ... 0 bar -13.775 ... 0 psi
Nominal operating pressure	-70 kPa -0.7 bar
Nominal operating pressure (psi)	-10.15 psi
Operating medium	Atmospheric air based on ISO 8573-1:2010 [7:-:]
Corrosion resistance classification CRC	1 - Low corrosion stress
PWIS conformity	VDMA24364-A1-L
Food-safe	See Supplementary material information
Ambient temperature	-10 ... 70 °C
Retention force at nominal operating pressure	134.4 N
Horizontal lateral force at nominal operating pressure	201 N
Vertical lateral force at nominal operating pressure	134.5 N
Product weight	55.3 g
Mounting type	Via vacuum port
Vacuum connection	M10
Colour	Black
Shore hardness	50 +/- 5
Materials note	Conforms to RoHS
Material suction cup	NBR