


# multiple distributor QSLV3-1/2-1/2-U

Part number: 190787

FESTO

3-fold, 360° orientable.



## Data sheet

Feature	Value
Size	Standard
Nominal size	6.9 mm
Type of seal on screw-in stud	coating
Assembly position	Any
Design structure	Push/pull principle
Container size	1
Operating pressure for entire temperature range	-0.095 ... 1 MPa
Operating pressure complete temperature range	-0.95 ... 10 bar
Operating pressure for entire temperature range	-13.775 ... 145 psi
Maritime classification	see certificate
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:-:-]
Note on operating and pilot medium	Lubricated operation possible
Corrosion resistance classification CRC	1 - Low corrosion stress
PWIS conformity	VDMA24364-B1/B2-L
Ambient temperature	-10 ... 60 °C
Max. tightening torque	30 Nm
Product weight	179 g
Number of outputs	3
Number of supply lines	1
Pneumatic connection, port 1	Male thread 1/2 NPT
Pneumatic connection, port 2	for tubing, 1/2" outside diameter
Ambient temperature Fahrenheit	14 ... 140 °F
Colour of release ring	Grey
Material of threaded plug	Nickel-plated brass
Materials note	Conforms to RoHS
Material housing	PBT
Material release ring	POM
Material of tubing seal	NBR
Material of tube retaining claw	High alloy steel, non-corrosive