


# differential pressure regulator

## LRL-1/2-NPT-QS-1/2-U

Part number: 190902  
Product to be discontinued

FESTO

Without manometer, with male thread and QS plug connector.  
Type to be discontinued. Available until 2023. See Support Portal for alternative products.



### Data sheet

Feature	Value
Controller function	Differential pressure, constant
Pneumatic connection, port 1	1/2 NPT
Pneumatic connection, port 2	QS-1/2
Mounting type	Threaded
Supply pressure 1 MPa	0 ... 0.9 MPa
Inlet pressure 1	0 ... 9 bar
Supply pressure 1 psi	0 ... 130.5 psi
Ambient temperature	0 ... 60 °C
Material housing	PBT-reinforced
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:-:-]
Assembly position	Any
Note on operating and pilot medium	Lubricated operation possible (subsequently required for further operation)
PWIS conformity	VDMA24364-B1/B2-L
Product weight	108 g
Material of threaded plug	Brass
Materials note	Conforms to RoHS