



shock absorber YSRW-16-26

Part number: 191197

FESTO

Self-adjusting, with progressive characteristic curve.



Data sheet

Feature	Value
Size	16
Stroke	26 mm
Cushioning	self-adjusting Soft characteristic
Assembly position	Any
Position detection	No
Max. impact speed	3 m/s
Reset time short	0.3 s
Reset time long	1 s
Mode of operation	single-acting pushing action
Corrosion resistance classification CRC	2 - Moderate corrosion stress
PWIS conformity	VDMA24364-B2-L
Ambient temperature	-10 ... 80 °C
Cushioning length	26 mm
Max. stop force	2,000 N
Max. energy consumption per stroke	35 J
Max. energy consumption per hour	68,000 J
Max. residual energy	0.16 J
Reset force	6 N
Product weight	190 g
Mounting type	with lock nut
Materials note	Conforms to RoHS
Material seals	NBR
Material housing	steel, galvanized
Material piston rod	High alloy steel