

angle compensator ESWA-3

Part number: 191205

FESTO

with ball joint, angle of rotation 15°.



Data sheet

Feature	Value
Angle compensation +/-	15 deg
Assembly position	Any
Design structure	Ball joint
Correlation to suction-cup holder	Size 3
Operating pressure	-0.95 ... 4 bar
Corrosion resistance classification CRC	1 - Low corrosion stress
PWIS conformity	VDMA24364-A1-L
Ambient temperature	0 ... 60 °C
Product weight	9 g
Mounting type	with external (male) thread
suction cup mounting	M4
Pneumatic connection	M4
Materials note	Conforms to RoHS
Material seals	NBR
Material housing	Aluminium Nickel-plated brass