


Push-in L-fitting QSMKL-1/16-5/32-U

Part number: 192814

FESTO

This product is only available if ordered from the Festo Corporation, USA.
Products to be discontinued. Available until 2011.



Data sheet

| Feature | Value |
|--|--|
| Size | Mini |
| Nominal size | 1.6 mm |
| Type of seal on screw-in stud | coating |
| Assembly position | Any |
| Container size | 1 |
| Design structure | Push/pull principle |
| Operating pressure | -0.95 ... 10 bar |
| Temperature dependent operating pressure | -0.95 ... 10 bar |
| Operating medium | Filtered compressed air Vacuum |
| Corrosion resistance classification CRC | 1 |
| Ambient temperature | -10 ... 60 °C |
| Authorisation | Germanischer Lloyd |
| Product weight | 15 g |
| Pneumatic connection | NPT1/16-27 for tubing, 5/32" outside diameter |
| Colour of release ring | Grey |
| Materials note | Conforms to RoHS |
| Materials information, housing | PBT |
| Release ring material data | POM |
| Materials information for tubing seal | NBR |
| Hose clamping segment material data | High alloy steel, non-corrosive |