


connecting cable KMYZ-3-24-2,5-LED-PUR-B

Part number: 193693

FESTO

For high speed valves



Data sheet

Feature	Value
Assembly position	Any
Switching position indicator	LED
Protection class	IP65
Ambient temperature	-10 ... 50 °C
Tightening torque	0.25 Nm
Product weight	50 g
Electrical connection	Angled socket / cable Square design/open end 2-pin / 2-wire
Cable structure	2x0,25
Cable diameter	3.4 mm
Cable length	2.5 m
Protective earth connection	Not available
Mounting type	On solenoid valve with M2 central screw
Materials note	Conforms to RoHS
Materials information, housing	PA
Materials information, cable sheaths	TPE-U(PUR)
Material information for crimp connectors	Bronze