

CPV14-EPR-PGU

End plate

Data sheet

Part no.: 193914

Page:1

Feature	Data/description
Air connection type	Sub-base
Operating pressure min.	0 bar
Operating pressure max.	10 bar
Minimum ambient temperature	-5 °C
Maximum ambient temperature	50 °C
Sound pressure level	82 dB(A)
Standard nominal flow rate	9000 l/min
Material of shock absorber insert	PE