


FRCS-1/8-D-MINI-KE

Service unit combination

Feature	Data/description
Size	Mini
Series	D
Actuator lock	Rotary knob with integrated lock
Assembly position	Vertical +/- 5°
Grade of filtration	40 µm
Condensate drain	manual rotary
Design structure	On/off valve Filter regulator with pressure gauge Proportional standard oil-mist lubricator Safety start-up valve
Max. condensate volume	22 cm ³
Bowl guard	Metal bowl guard
Pressure gauge	with pressure gauge
Pressure control range	2,5 - 12 bar
Inlet pressure 1	3,5 - 16 bar
Max. pressure hysteresis	0,15 bar
Standard nominal flow rate	550 l/min
Operating medium	Compressed air
Medium temperature	-10 - 60 °C
Ambient temperature	-10 - 60 °C
Product weight	1.300 g
Mounting type	Optional Line installation with accessories
Pneumatic connection, port 1	G1/8
Pneumatic connection, port 2	G1/8



FRCS-1/8-D-MINI-KE

Service unit combination

Feature	Data/description
Materials information, housing	Zinc die-casting
Materials information for bowl	PC