



FRCS-3/8-D-MIDI-KF

Service unit combination

| Feature | Data/description |
|----------------------------|---|
| Size | Midi |
| Series | D |
| Actuator lock | Rotary knob with integrated lock |
| Assembly position | Vertical +/- 5° |
| Grade of filtration | 40 µm |
| Condensate drain | manual rotary |
| Design structure | Branching module Pressure sensor On/off valve Filter regulator with pressure gauge Proportional standard oil-mist lubricator Safety start-up valve |
| Max. condensate volume | 43 cm ³ |
| Bowl guard | Metal bowl guard |
| Pressure gauge | with pressure gauge |
| Output pressure 3 | 2,5 - 12 bar |
| Pressure control range | 2,5 - 12 bar |
| Inlet pressure 1 | 3,5 - 16 bar |
| Max. pressure hysteresis | 0,3 bar |
| Standard nominal flow rate | 1.150 l/min |
| Operating medium | Compressed air |
| Medium temperature | -10 - 60 °C |
| Ambient temperature | -10 - 60 °C |
| Product weight | 4.240 g |
| Mounting type | Optional Line installation with accessories |



FRCS-3/8-D-MIDI-KF

Service unit combination

| Feature | Data/description |
|--------------------------------|------------------|
| Pneumatic connection, port 1 | G3/8 |
| Pneumatic connection, port 2 | G3/8 |
| Pneumatic connection, port 3 | G1/2 |
| Materials information, housing | Zinc die-casting |
| Materials information for bowl | PC |