

# barbed fitting CN-M5-PK-2

Part number: 19521

FESTO

For plastic tubing PAN, PUN, PP, PU, PR, with sealing ring



## Data sheet

Feature	Value
Nominal size	1.5 mm
Type of seal on screw-in stud	Sealing ring
Operating pressure complete temperature range	-0.95 ... 10 bar
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:-:-]
Note on operating and pilot medium	Lubricated operation possible (subsequently required for further operation)
PWIS conformity	VDMA24364-B1/B2-L
Ambient temperature	0 ... 60 °C
Pneumatic connection, port 1	Male thread M5
Pneumatic connection, port 2	For tubing outside diameter 3 mm
Materials note	Conforms to RoHS
Material housing	Steel