

CPE10-M1BH-5/3E-QS-4

Solenoid valve

Data sheet

Part no.: 196864

Page:1

Feature	Data/description
Switching function	5/3-way valve, exhausted in mid-position
Switching function short code	5/3
Function in mid-position (neutral)	Exhausted
Direction of flow reversible	No
Operating principle	Slide
Shape of function component	Piston
With exhaust flow control	No
Type of regulation	Indirect
Control type	Bistable
Type of reset	Mechanical spring
Type of mounting	Screw
Installation position	Any
Nominal size	4 mm
Operating pressure min.	3 bar
Operating pressure max.	8 bar
Minimum ambient temperature	-5 °C
Maximum ambient temperature	50 °C
Minimum medium temperature	-5 °C
Maximum medium temperature	50 °C
Type of connection, air supply	Push-in
Nominal size of tubing connection, suppl	4
Air connection type power port	Push-in
Nominal size of tubing connection, worki	4
Type of connection, exhaust	Female thread
Connecting thread, exhaust port	M 7
Air connection type aux. pilot air suppl	Internal
Air connection type aux. pilot air exhau	Female thread
Connecting thread for aux. pilot air exh	M 3
Type pilot control air Supply and exhaus	Internal pilot air, ducted pilot exhaust
Actuation/reset	Double solenoid, spring-centred
Manual override	push to reset

CPE10-M1BH-5/3E-QS-4

Solenoid valve

Data sheet

Part no.: 196864

Page:2

Feature	Data/description
Operating status display	No
Material of cap	PA
Material of housing	AL, die-cast metal
Material of seals	NBR-Elastomer
Product weight	0,073 kg
Standard nominal flow rate 1 - 2	180 l/min
Standard nominal flow rate 2 - 3	180 l/min
Standard nominal flow rate 1 - 4	180 l/min
Standard nominal flow rate 4 - 3/5	180 l/min
Standard nominal flow rate (mid-pos.)	180 l/min
Response time OFF/OVER (dom.)	16 ms
Response time OFF/OVER	20 ms
Voltage type	DC
Nominal voltage	24 V
Power consumption (DC)	1 W
Medium	Filtered compr. air (40 µm) (may be lubricated)
Degree of protection	IP65