

fluid separator CQA-28

Part number: 196984

FESTO

For dry air.



Data sheet

| Feature | Value |
|---|---|
| Nominal size | 20 mm |
| Assembly position | Vertical |
| Container size | 1 |
| Design structure | Push/pull principle |
| Operating pressure complete temperature range | -0.95 ... 7 bar |
| Temperature dependent operating pressure | -0.95 ... 10 bar |
| Operating medium | Compressed air in accordance with ISO8573-1:2010 [7:-:-] |
| Note on operating and pilot medium | Lubricated operation possible (subsequently required for further operation) |
| Corrosion resistance classification CRC | 2 - Moderate corrosion stress |
| PWIS conformity | VDMA24364 zone III |
| Medium temperature | -25 ... 75 °C |
| Ambient temperature | -25 ... 70 °C |
| Product weight | 18 g |
| Pneumatic connection, port 1 | Push-in sleeve CQ-28 |
| Pneumatic connection, port 2 | Push-in sleeve CQ-28 |
| Materials note | Conforms to RoHS |
| Material housing | Brass |