


manifold block MHP1-PR10-3-PI-PCB

Part number: 197246

FESTO

For mounting semi in-line valves MHP1-....-PI to PCBs



Data sheet

Feature	Value
Max. number of valve positions	10
Operating pressure	0 ... 8 bar
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (subsequently required for further operation)
Corrosion resistance classification CRC	2 - Moderate corrosion stress
PWIS conformity	VDMA24364-B2-L
Ambient temperature	0 ... 40 °C
Mounting method for valve	with internal (female) thread
Pneumatic connection, port 1	M5
Pneumatic connection, port 3	M5
Material of connecting plate	Wrought Aluminium alloy