

manifold block MHA2-PR10-3-M5

Part number: 197451

FESTO

for manifold block valves MHA2-...-HC/TC



Data sheet

Feature	Value
Max. number of valve positions	10
Corrosion resistance classification CRC	2 - Moderate corrosion stress
PWIS conformity	VDMA24364-B1/B2-L
Mounting method for sub-base	with through hole with top-hat rail
Mounting method for valve	with internal (female) thread
Pneumatic ports 1/33	M7
Pneumatic connection, port 2	M5
Pneumatic ports 3/11	M7
Material of connecting plate	Wrought Aluminium alloy