

# One-way flow control valve GRLA-E-1/8-QS-8

Part number: 197484

FESTO

For exhaust air flow control, with swivel joint.

This product is only available if ordered from Festo Korea Co. Ltd.



## Data sheet

Feature	Value
Valve function	One-way flow control function
Pneumatic connection, port 2	R1/8
Mounting type	Threaded
Operating pressure	0 ... 8 bar
Ambient temperature	0 ... 60 °C
Operating medium	Filtered compressed air
Medium temperature	0 ... 60 °C
Product weight	45.6 g
Materials information for screw-in stud	Brass
Materials note	Contains PWIS substances
Materials information for seals	NBR