

DUO spiral plastic tubing PUN-4X0,75-S-1,5-DUO-BS

Part number: 197619

FESTO

Highly flexible, hydrolysis resistant to a great extent



Data sheet

Feature	Value
Working length	1.5 m
Outside diameter	4 mm
Block length	0.668 m
Inside diameter	2.6 mm
Coil diameter	25 mm
Number of windings	70
Temperature dependent operating pressure	-0.95 ... 10 bar
Authorisation	TÜV
Certificate issuing department	B 013277 0506 00
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:::]
PWIS conformity	VDMA24364-B2-L
Ambient temperature	-35 ... 60 °C
Product weight	84 g
Pneumatic connection	For push-in connector outside diameter 4 mm for barbed connector internal diameter 3 mm with nut for barbed connector internal diameter 3 mm
Colour	blue/black
Shore hardness	D 52 +/-3
Material tubing	TPE-U(PU)