


axial kit EAMM-A-D60-80P

Part number: 1977073

★ Core product range

Suitable for electric drives.

FESTO



Data sheet

Feature	Value
Assembly position	Any
PWIS conformity	VDMA24364-B2-L
Storage temperature	-25 ... 60 °C
Relative air humidity	0 - 95 %
Protection class	IP40
Ambient temperature	-10 ... 60 °C
Transferable torque	17 Nm
Product weight	1,040 g
Interface code, actuator	D60A D60B D60C
Interface code, motor in	80P
Materials note	Conforms to RoHS