

# spiral plastic tubing

## PPS-4-7,5-1/4-BL

Part number: 19798

FESTO

With 2 rotatable fittings and sealing rings, polyamide (not approved for use in the food industry).



### Data sheet

Feature	Value
Working length	7.5 m
Outside diameter	6.3 mm
Block length	0.34 m
Inside diameter	4.7 mm
Coil diameter	75 mm
Number of windings	44
Temperature dependent operating pressure	-0.95 ... 21.2 bar
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7::-]
Corrosion resistance classification CRC	1 - Low corrosion stress
PWIS conformity	VDMA24364-B2-L
Ambient temperature	-30 ... 80 °C
Nominal tightening torque	11 Nm
Tolerance for nominal tightening torque	± 20 %
Product weight	249 g
Pneumatic connection, port 1	Male thread G1/4
Pneumatic connection, port 2	Male thread G1/4
Colour	blue
Material of connecting thread	Brass
Materials note	Conforms to RoHS
Material buckling protection	Steel Galvanised
Material tubing	Polyamide 12