

union nut MCK-PK-3-KU

Part number: 211289

FESTO

Polymeric design.



Data sheet

Feature	Value
Size	Female thread M6x0.75
Operating pressure for entire temperature range	0 ... 1 MPa
Operating pressure complete temperature range	0 ... 10 bar
Operating pressure for entire temperature range	0 ... 145 psi
PWIS conformity	VDMA24364-B2-L
Ambient temperature	-10 ... 60 °C
Pneumatic connection, port 1	For tubing outside diameter 4 mm for barbed connector internal diameter 3 mm with nut
Material of union nut	POM
Materials note	Conforms to RoHS