

union nut MCK-PK-9-KU

Part number: 211293

FESTO

Polymeric design.



Data sheet

| Feature | Value |
|---|--|
| Size | Female thread M16x1 |
| Operating pressure for entire temperature range | 0 ... 1 MPa |
| Operating pressure complete temperature range | 0 ... 10 bar |
| Operating pressure for entire temperature range | 0 ... 145 psi |
| PWIS conformity | VDMA24364-B2-L |
| Ambient temperature | -10 ... 60 °C |
| Pneumatic connection, port 1 | for barbed connector internal diameter 9 mm with nut |
| Material of union nut | POM |
| Materials note | Conforms to RoHS |