

Plastic tubing PL-9-BL

Part number: 2238

FESTO

For CK and N connectors.

The maximum pressure value is permissible at the maximum temperature.



Data sheet

| Feature | Value |
|--|--|
| Outside diameter | 11.6 mm |
| Bending radius relevant for flow rate | 85 mm |
| Inside diameter | 9 mm |
| Temperature dependent operating pressure | 0 ... 7 bar |
| Operating medium | Compressed air in accordance with ISO8573-1:2010 [7:-:-] |
| Ambient temperature | -10 ... 35 °C |
| Product weight according to length | 0.049 kg/m |
| Colour | blue |
| Shore hardness | A 85 +/-3 |
| Materials note | Free of copper and PTFE Conforms to RoHS |
| Materials information for tubing | PVC-P |