

axial kit EAMM-A-D60-100A-S1

Part number: 2256700

FESTO

Suitable for electric drives.



Data sheet

| Feature | Value |
|--------------------------|--------------------|
| Assembly position | Any |
| PWIS conformity | VDMA24364 zone III |
| Storage temperature | -25 ... 60 °C |
| Relative air humidity | 0 - 95 % |
| Protection class | IP65 |
| Ambient temperature | -10 ... 60 °C |
| Transferable torque | 17 Nm |
| Product weight | 1,170 g |
| Interface code, actuator | D60A D60B |
| Interface code, motor in | 100A |
| Materials note | Conforms to RoHS |