


# axial kit EAMM-A-P6-38A-40G

Part number: 2297645

FESTO

Suitable for electric drives.



## Data sheet

Feature	Value
Assembly position	Any
PWIS conformity	VDMA24364-B2-L
Storage temperature	-25 ... 60 °C
Relative air humidity	0 - 95 %
Protection class	IP40
Ambient temperature	-10 ... 60 °C
Transferable torque	6.5 Nm
Product weight	190 g
Interface code, actuator	P6-38A
Interface code, motor in	40G
Interface code, coupling housing	38A.2
Materials note	Conforms to RoHS