


# butterfly valve

## VZFB-D-50-WW-V2V2V

Part number: 2466823  
Product to be discontinued

FESTO

Nominal width DN50, with welded ends, DIN 11850, FPM, material 1.4301.  
Type to be discontinued. Available until 2022. See Support Portal for alternative products.



### Data sheet

Feature	Value
Design structure	2-way disc valve
Type of actuation	manual
Sealing principle	soft
Assembly position	Any
Mounting type	Line installation
Process valve connection	Weld-on ends/weld-on ends
Nominal diameter DN	50
Flow direction	reversible
Nominal pressure of process valve	10
Actuation torque	14 Nm
Based on the standard	DIN 11851
Medium	Water Neutral fluids
Medium temperature	-15 ... 140 °C
Materials note	Contains PWIS substances Conforms to RoHS
Food-safe	See Supplementary material information
Material housing	High alloy steel, non-corrosive
Material number for housing	1.4301
Material disc	High alloy steel, non-corrosive
Material number for disc	1.4301
Material shaft	High alloy steel, non-corrosive
Material number for shaft	1.4301
Product weight	1,600 g
Corrosion resistance classification CRC	3 - High corrosion stress