

bellows cylinder EB-80-45

Part number: 2748904

FESTO

Maintenance-free, no stick/slip effect.



Data sheet

Feature	Value
Size	80
Required installation diameter	95 mm
Stroke	45 mm
Max height when extended	110 mm
Max. tipping angle	15 deg
Max. offset	10 mm
Min. installation height	65 mm
Mode of operation	single-acting
Operating pressure	0 ... 8 bar
Operating medium	Compressed air to ISO 8573-1:2010 [-:::4]
Note on operating and pilot medium	Lubricated operation not possible
Corrosion resistance classification CRC	0 - No corrosion stress
PWIS conformity	VDMA24364-B1/B2-L
Ambient temperature	-40 ... 70 °C
Reset force	200 N
Product weight	500 g
Mounting type	with internal (female) thread
Pneumatic connection	G1/4
Materials note	Conforms to RoHS
Material bellows	CR
Material housing	Aluminium casting