

parallel kit EAMM-U-86-D50-60H-102-S1

Part number: 2803325

FESTO

Suitable for electric drives.



Data sheet

| Feature | Value |
|--------------------------|-----------------------|
| Size | 86 |
| Assembly position | Any |
| Gear unit ratio | 1:1 |
| Max. speed | 5,000 1/min |
| PWIS conformity | VDMA24364 zone III |
| Storage temperature | -25 ... 60 °C |
| Relative air humidity | 0 - 95 % |
| Protection class | IP65 |
| Ambient temperature | -10 ... 60 °C |
| Mass moment of inertia | 175 kgmm ² |
| No-load driving torque | 0.25 Nm |
| Transferable torque | 9.5 Nm |
| Product weight | 2,520 g |
| Interface code, actuator | D50B |
| Interface code, motor in | 60H |
| Materials note | Conforms to RoHS |