


axial kit EAMM-A-D32-60G

Part number: 2946758

FESTO

Suitable for electric drives.



Data sheet

Feature	Value
Assembly position	Any
PWIS conformity	VDMA24364-B2-L
Storage temperature	-25 ... 60 °C
Relative air humidity	0 - 95 %
Protection class	IP40
Ambient temperature	-10 ... 60 °C
Transferable torque	6.5 Nm
Product weight	540 g
Interface code, actuator	D32A D32B D32C
Interface code, motor in	60G
Materials note	Conforms to RoHS