


# axial kit EAMM-A-D80-80G-S1

Part number: 2946764

FESTO

Suitable for electric drives.



## Data sheet

Feature	Value
Assembly position	Any
PWIS conformity	VDMA24364-B2-L
Storage temperature	-25 ... 60 °C
Relative air humidity	0 - 95 %
Protection class	IP65
Ambient temperature	-10 ... 60 °C
Transferable torque	60 Nm
Product weight	1,990 g
Interface code, actuator	D80B
Interface code, motor in	80G
Materials note	Conforms to RoHS