



Cartridge EGZ-10-

Part number: 30910

FESTO



Datasheet

Feature	Value
Mode of operation	Single, pushing
Sensing type	None
Type of cushioning	None
Piston, nominal size	10 mm
Stroke	0 mm
Minimum stroke with B2 = 0	1 mm
Maximum stroke with B2 = 0	15 mm
Thread type (piston rod) (KK)	M
Thread diameter (metric)	4 mm
Thread length (piston rod)	10 mm
Overall length	27,5 mm
Silicone status	Free
Connection type cover cap	Thread
Thread type (cover cap)	M
Thread diameter (metric)	5 mm