

LOE-1/2-S-B

Lubricator

Data sheet

Part no.: 30972

Page:1

Feature	Data/description
Design lubricator	Direct proportional
Modular design	Yes
Input pressure 1 min. (bar)	0,5 bar
Input pressure 1 max. (bar)	14 bar
Thread for port 1	G 1/2
Thread for port 2	G 1/2
Type of mounting	Hole/in-line
Minimum ambient temperature	-10 °C
Maximum ambient temperature	60 °C
Minimum medium temperature	-10 °C
Maximum medium temperature	60 °C
Minimum flow for lubricator operation	55 l/min
Oil capacity max.	200 cm³
Oil viscosity	23.0
Metal bowl guard	No
Material of housing	PA-reinforced
Material of bowl	PA
Contains silicone materials	Yes
Standard nominal flow rate 1-2	5500 l/min
Operating medium input 1	Compressed air
Operating medium output 2	Compressed air, lubricated