



proximity sensor SMPO-1-H-B

Part number: 31008

FESTO

Without mounting kit



Data sheet

Feature	Value
Design	Block design
Measuring principle	Magnetic
Operating pressure	2 ... 6 bar
Operating medium	Compressed air in accordance with ISO8573-1:2010 [6:4:4]
Note on operating and pilot medium	Lubricated operation not possible
Ambient temperature	-15 ... 60 °C
Reproducibility of switching value	+/- 0,2 mm
Switch-on time	< 30 ms
Switch-off time	< 25 ms
Mounting type	with through hole with accessories
Valve function	3/2
Pneumatic connection	Barbed fitting PK-3
Product weight	14 g
Material housing	Brass PA POM
Operating status display	Optical
Protection class	IP65
PWIS conformity	VDMA24364-B2-L