

HE-1/8-S-B

Soft-start valve

Data sheet

Part no.: 33016

Page:1

Feature	Data/description
Switching function	3/2-way valve, normally closed
Switching function short code	3/2
Direction of flow reversible	No
Operating principle	Slide
Shape of function component	Sub-base
With exhaust flow control	No
Type of regulation	Direct
Control type	Bistable
Type of mounting	Screw + line
Installation position	Any
Nominal size	7,2 mm
Operating pressure min.	1 bar
Operating pressure max.	14 bar
Minimum ambient temperature	-10 °C
Maximum ambient temperature	60 °C
Minimum medium temperature	-10 °C
Maximum medium temperature	60 °C
Type of connection, air supply	Thread
Connecting thread, supply port	G 1/8
Air connection type power port	Thread
Connecting thread, working port	G 1/8
Type of connection, exhaust	Thread
Connecting thread, exhaust port	G 1/8
Actuation/reset	Lever, detenting
Standard nominal flow rate 1 - 2	950 l/min
Standard nominal flow rate 2 - 3	370 l/min
Medium	Compressed air, filtered 50 µm (may be lubricated)