

foot mounting DAMH-Q12-6

Part number: 3371840

FESTO



Data sheet

Feature	Value
Size	6
Assembly position	Any
Corrosion resistance classification CRC	1 - Low corrosion stress
PWIS conformity	VDMA24364-B2-L
Ambient temperature	0 ... 60 °C
Max. tightening torque	1 Nm
Product weight	27 g
Mounting type	with through hole
Materials note	Conforms to RoHS
Material bracket	steel, galvanized