


front unit

ERMH-11-E17-30

Part number: 3385153
Product to be discontinued

FESTO

Type to be discontinued. Available until 2022. See Support Portal for alternative products.



Data sheet

Feature	Value
Size	11
Design structure	Electro-mechanical rotary module
Assembly position	Any
Rotation angle	Endless
Gear unit ratio	30:1
Nominal torque	1.8 Nm
Repetition accuracy	±0,01 °
Max. axial force	300 N
Product weight	1,298 g
Duty cycle	100 %
Nominal motor current	0.74 A
Motor type	Servomotor
Max. output speed	200 1/min
Nominal operating voltage, AC	230 V
Nominal motor power	22.1 W
Peak current	1.5 A
Max. pull-out torque static	40 Nm
Peak torque	4.5 Nm
Permissible mass moment of inertia of load	0.006 kgm ²
Protection class	IP40
Ambient temperature	0 ... 40 °C
Materials note	Conforms to RoHS