


clevis foot LNG-125

Part number: 33896

FESTO



Data sheet

Feature	Value
Size	125
Based on the standard	ISO 15552 (previously also VDMA 24652, ISO 6431, NF E49 003.1, UNI 10290)
Corrosion resistance classification CRC	1 - Low corrosion stress
PWIS conformity	VDMA24364-B2-L
Ambient temperature	-40 ... 80 °C
Product weight	2,545 g
Materials note	Conforms to RoHS
Material mounting	Nodular graphite cast iron
Material bearing	PA