



Solenoid valve

JMYH-5/2-2,3-L-LED

Part number: 34304

FESTO

With solenoid coils and manual override, without plug sockets.



Data sheet

| Feature | Value |
|---------------------------------|--|
| Valve function | 5/2 bistable |
| Standard nominal flow rate | 180 l/min |
| Operating pressure | 2 ... 8 bar |
| Design structure | Piston slide |
| Protection class | IP40 with plug socket |
| Nominal size | 2.3 mm |
| Type of piloting | Piloted |
| Switching time reversal | 7 ms |
| Duty cycle | 100% |
| Characteristic coil data | 24V DC: 1,8W |
| Operating medium | Dried compressed air, lubricated or unlubricated |
| Medium temperature | -5 ... 50 °C |
| Ambient temperature | -5 ... 50 °C |
| Product weight | 95 g |
| Mounting type | with through hole |
| Pneumatic connection, port 1 | Sub-base Manifold module |
| Pneumatic connection, port 2 | Sub-base Manifold module |
| Pneumatic connection, port 3 | Sub-base Manifold module |
| Pneumatic connection, port 4 | Manifold module |
| Pneumatic connection, port 5 | Manifold module |
| Materials information for seals | NBR |
| Materials information, housing | Aluminium die cast |