


# guide unit FENG-63- -GF

Part number: 34484

FESTO

with plain-bearing guide, serves for protection against rotation,  
provides a high accuracy of guidance.



## Data sheet

Feature	Value
Size	63
Stroke	10 ... 500 mm
Assembly position	Any
Guide	Plain-bearing guide
Design structure	Guide
PWIS conformity	VDMA24364-B2-L
Ambient temperature	-20 ... 80 °C
Displacement force	50 N
Additional mass factor per 10 mm of stroke	48 g
Basic weight for 0 mm stroke	5,540 g
Additional weight per 10 mm stroke	48 g
Centre of gravity of moving mass with 0 mm stroke	69 mm
Additional allowance for centre of gravity of moving mass per 10 mm stroke	4.6 mm
Mounting type	with internal (female) thread
Materials note	Conforms to RoHS
Material of guide component	High alloy steel
Material housing	Anodised wrought aluminium alloy
Material yoke plate	Anodised wrought aluminium alloy