


# Two-hand control block ZSB-1/8

Part number: 3527

FESTO

Safety component with two-hand operation.



## Data sheet

Feature	Value
Nominal size	4 mm
Type of actuation	pneumatic
Design structure	Poppet valve with spring return
Operating pressure	3 ... 8 bar
Standard nominal flow rate	50 l/min
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:4:4]
CE mark (see declaration of conformity)	to EU directive for machinery
Ambient temperature	-10 ... 60 °C
Product weight	490 g
Mounting type	with through hole with internal (female) thread Optional
Auxiliary pilot air port 12	G1/8
Auxiliary pilot air port 14	G1/8
Pneumatic connection, port 1	G1/8
Pneumatic connection, port 2	G1/8
Pneumatic connection, port 3	G1/8
Pneumatic connection, port 4	G1/8
Pneumatic connection, port 5	G1/8
Materials information for cover	Aluminium die cast
Materials information for seals	NBR
Materials information, housing	Wrought Aluminium alloy Anodised