


mounting plate

VAME-S7-P-N-V14-A

Part number: 3581412

FESTO



Data sheet

Feature	Value
Assembly position	Any
Operating pressure MPa	0 ... 1 MPa
Operating pressure	0 ... 10 bar 0 ... 145 psi
Operating medium	Compressed air in accordance with ISO8573-1:2010 [-::-]
Corrosion resistance classification CRC	4 - Very high corrosion stress
PWIS conformity	VDMA24364 zone III
Protection class	IP65
Mounting type	with through hole
Pneumatic connection, port 1	M5 NAMUR port pattern
Pneumatic connection, port 2	Flange 1/4 NAMUR port pattern
Pneumatic connection, port 3	G1/4
Materials note	Conforms to RoHS
Material seals	NBR
Material plate	Aluminium (Ematal coated)