

barbed L-fitting LCNH-3/8-PK-6

Part number: 35990

FESTO

Rotatable, with extended housing, for plastic tubing PAN, PUN, PP, PU,
PR, with sealing ring.



Data sheet

Feature	Value
Nominal size	4.9 mm
Type of seal on screw-in stud	Sealing ring
Operating pressure complete temperature range	-0.95 ... 10 bar
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:-:-]
Note on operating and pilot medium	Lubricated operation possible (subsequently required for further operation)
Corrosion resistance classification CRC	2 - Moderate corrosion stress
PWIS conformity	VDMA24364-B1/B2-L
Ambient temperature	0 ... 60 °C
Pneumatic connection, port 1	Male thread G3/8
Pneumatic connection, port 2	For tubing outside diameter 8 mm
Materials note	Conforms to RoHS
Material housing	Aluminium Zinc die-casting