

# quick coupling plug KS5-CK-13


Part number: 4096

Product to be discontinued

FESTO

For self-closing quick coupling connectors.

Type to be discontinued. Available until 2019. See Support Portal for alternative products.



## Data sheet

Feature	Value
Nominal size	11.7 mm
Operating pressure complete temperature range	0 ... 12 bar
Standard nominal flow rate	2,043 l/min
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:-:-]
Note on operating and pilot medium	Lubricated operation possible
Corrosion resistance classification CRC	1 - Low corrosion stress
Ambient temperature	-10 ... 60 °C
Product weight	251 g
Pneumatic connection, port 1	CK-13