


# axial kit EAMM-A-V32-57A

Part number: 4597016

★ Core product range

FESTO



## Data sheet

Feature	Value
Nominal length	41.5 mm
Assembly position	Any
Max. speed	10,000 1/min
PWIS conformity	VDMA24364-B2-L
Storage temperature	-25 ... 60 °C
Relative air humidity	0 - 95 %
Protection class	IP40
Ambient temperature	-10 ... 60 °C
Mass moment of inertia	0.19 kgmm <sup>2</sup>
Transferable torque	1.5 Nm
Product weight	180 g
Interface code, actuator	V32
Interface code, motor in	57A
Materials note	Conforms to RoHS