

Silencer U-M5

Part number: 4645

FESTO



Data sheet

Feature	Value
Assembly position	Any
Operating pressure	0 ... 10 bar
Flow rate to atmosphere	320 l/min
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:-:-]
Note on operating and pilot medium	Lubricated operation possible (subsequently required for further operation)
Sound pressure level	70 dB(A)
Ambient temperature	-10 ... 70 °C
Pneumatic connection	M5
Materials information for silencer insert	Bronze
Materials information for screw-in stud	Brass
Materials note	Free of copper and PTFE Conforms to RoHS