


# parallel kit EAMM-U-87-T46-60P-114

Part number: 4824069

★ Core product range

FESTO



## Data sheet

Feature	Value
Size	87
Centre-to-centre distance	114 mm
Assembly position	Any
Gear unit ratio	1:1
Max. speed	3,000 1/min
PWIS conformity	VDMA24364 zone III
Storage temperature	-20 ... 60 °C
Relative air humidity	0 - 95 %
Protection class	IP40
Ambient temperature	0 ... 50 °C
Mass moment of inertia	41.2 kgmm <sup>2</sup>
No-load driving torque	0.22 Nm
Transferable torque	3.5 Nm
Product weight	913 g
Interface code, actuator	T46
Interface code, motor in	60P 60PA
Materials note	Conforms to RoHS