


silencer U-PK-4

Part number: 4932

FESTO

For reducing noise and avoiding contamination at the exhaust ports of pneumatic components.



Data sheet

| Feature | Value |
|------------------------------------|--|
| Assembly position | Any |
| Operating pressure MPa | 0 ... 1 MPa |
| Operating pressure | 0 ... 10 bar |
| Flow rate to atmosphere | 580 l/min |
| Operating medium | Compressed air in accordance with ISO8573-1:2010 [7:-:-] |
| Note on operating and pilot medium | Lubricated operation possible |
| PWIS conformity | VDMA24364-B1/B2-L |
| Sound pressure level | 77 dB(A) |
| Ambient temperature | -10 ... 70 °C |
| Product weight | 4.1 g |
| Pneumatic connection | PK-4 |
| Material of silencer insert | Bronze |
| Material of threaded plug | Brass |
| Materials note | Conforms to RoHS |