


# coupling

## EAMD-56-54-19-23X27

Part number: 5215476

FESTO



### Data sheet

Feature	Value
Holder diameter 1	19 mm
Holder diameter 2	23 mm
Size	56
Nominal length	54.5 mm
Assembly position	Any
Max. speed	5,500 1/min
PWIS conformity	VDMA24364-B2-L
Storage temperature	-25 ... 60 °C
Relative air humidity	0 - 95 %
Ambient temperature	-25 ... 60 °C
Mass moment of inertia	172 kgmm <sup>2</sup>
Transferable torque	60 Nm
Product weight	464 g
Materials note	Conforms to RoHS