

Manifold block MHP3-PR6-3

Part number: 525218

FESTO

For MHP3-...-HC/TC semi in-line valves



Data sheet

Feature	Value
Max. number of valve positions	6
Corrosion resistance classification CRC	2
Mounting method for sub-base	with through hole with top-hat rail
Mounting method for valve	with internal (female) thread
Pneumatic ports 1/33	G1/4
Pneumatic ports 3/11	G1/4
Materials note	Free of copper and PTFE
Materials information for sub-base	Wrought Aluminium alloy